Latex Gloves Powdered

Sizes XS - XL

VCA2 Patasheet AQL 4 Powdered Latex Gloves ther Surface * High Tensile Strength * Non Sterile * Single Use

Glove Specifications

Size	Weight	Length	Palm Width		Thickness	
	g/pc	mm	mm	Cuff	Palm	Finger
XS	3.8 ± 0.2	240	75 ± 10	0.07 ± 0.02	0.085 ± 0.02	0.10 ± 0.02
S	4.3 ± 0.2	240	80 ± 10	0.07 ± 0.02	0.085 ± 0.02	0.10 ± 0.02
М	4.8 ± 0.2	240	95 ± 10	0.07 ± 0.02	0.085 ± 0.02	0.10 ± 0.02
L	5.3 ± 0.2	240	111 ± 10	0.07 ± 0.02	0.085 ± 0.02	0.10 ± 0.02
XL	5.8 ± 0.2	240	115 ± 10	0.07 ± 0.02	0.085 ± 0.02	0.10 ± 0.02
Tensil	e strength befo	re ageing (all	Load @ peak	MPA	Min.14	
Elong	ation before ag	eing (all glove	600%			



AQL4

EN445 Parts 1, 2 & 3

EN384

Class 1 Medical Device

MDD 93/42/EEC

Performance Requirements

Test	Related Defects	Inspection Level	AQL
Water Leak at Final Release	Holes	G-1 Single Sampling Plan	4

Manufacturing Standards

Maunfacturing Standards	Incompliance with ISO 9001:2008
Presentation	Standard: 100 gloves per dispenser box;
	10 dispenser boxes per Carton
Glove Care	Should not store under direct sunlight or at high heat and humid conditions. Single use only. Avoid high polar solvent.



General Details

Material	Natural Rubber Latex
Surface Finish	Powdered
Colour	Natural
Geometry	Ambidextrous
Texture	Fully Textured (Palm Textured)
Cuff and Finishing	Beaded